

Collimated UV light source system


<https://search.labfacilities.wur.nl/SearchDetail.aspx?deviceid=673ab033-4031-4911-94d6-25ad0b3b7d7f>

Brand

Bachur & Associates

Type

LS-150X-10



Contact

Daniella Stijnen (daniella.stijnen@wur.nl)

Organisation

Agrotechnology and Food Sciences

Department

Shared Research Facilities

Description

In photolithography and related applications, it is important that the light intensity is uniform over the entire substrate surface and constant in time. This can be achieved by generating a collimated light beam using mirrors and lenses. This light source generates a uniform beam of UV light with a diameter of 150 mm (6") and an intensity of approximately 10 mW/cm² (at 260 nm).

This equipment is located at Surfex (Plus Ultra, Bronland 12, Wageningen Campus). Are you interested in using this equipment or would you like to know more? You can contact Wout Knobens (Surfex) for information about the availability, technical details and possibilities for your specific application.

Technical Details

Light source: 1000 W Hg/Xe lamp

Mirror sets

- DUV (260 nm);
- MUV (310 nm).

Beam parameters

- diameter: 150 mm (6");
- divergence: 2 °

Control

- intensity controlling power supply system;
- programmable shutter.

Applications

- photoresist patterning;
- photocurable coatings.